

# ULTRA LOW LEVEL MONITOR

## PURPOSE

This wide range tritium monitoring station is designed to meet monitoring requirements established by NESHAP and EPA 40CFR or for DOE establishments for the determination of ultra low levels of airborne tritium.

## SENSITIVITY AND RANGE

Limits of resolution attained by this instrument is  $10^{-9}$  Ci/m<sup>3</sup> or even lower. Using linear as well as proportional chamber technology, the upper limit of useful measurement can be extended to 10 Ci/m<sup>3</sup> or higher.

## DISCRIMINATION

Separate measurements for the elemental as well as the oxide forms of tritium are provided. The instrument discriminates against all other airborne radioactive materials.

## COMPUTER DATA ACQUISITION AND DISPLAY

A user friendly icon based P.C. system is used for the retention and display of all measurement, supervisory and alarm status information.

## METHOD

Two high level linear ionization chambers and two low level proportional counters are used to span the total range of measurement. One pair of high and low level units are used to measure total tritium concentration and the other pair is used to measure the elemental form only. An automatically regenerating drying systems is used for separation of the chemical forms.



## MODEL 93 -WR - T - HTO

SEPARATE SAMPLE LINES FOR ELEMENTAL AND OXIDE FORMS, ULTRA HIGH SENSITIVITY TO  $10^{-9}$  Ci/m<sup>3</sup>, WIDE RANGE TO 10 Ci/m<sup>3</sup> STATION BY USING BOTH PROPORTIONAL COUNTERS AND LINEAR IONIZATION CHAMBERS



1160 US ROUTE 50  
MILFORD, OHIO 45150-9705  
TELEPHONE (513) 248-2400  
FACSIMILE (513) 248-2402  
E-MAIL sales@overhoff.com  
WEB www.OVERHOFF.com

**TECHNICAL SPECIFICATIONS SHORT**

<b>FORM</b>	<b>0 - 10 Ci/m<sup>3</sup></b>
Range	$\times 10^{-9} \text{ Ci/m}^3$
Sensitivity	19" color video terminal showing all current and trend data for and supervisory information.
Display	
measurements,	
Accuracy	+10 %, and/or $10^{-9} \text{ Ci/m}^3$
Response Rate	Varies with measurement level, up to minutes at very low levels to 1 at the upper end of the range
30 second	
Alarms	Set point alarms for each channel, supervisory alarms for sample flow counter for flow failure
High/Low Change Over:	Automatic changeover to prevent contamination of the low level measurement system
Volumes of Chambers	Linear: 2 liters nominal Proportional: 4 liters nominal
Counter Gas Flow	Adjustable from 0.1 lpm to 1 lpm
Enclosure	Standard 19" relay rack NEMA 12 enclosure, 72" high



1160 US ROUTE 50 MILFORD, OHIO 45150-9705  
TELEPHONE (513) 248-2400 FACSIMILE  
(513) 248-2402 E-MAIL [sales@overhoff.com](mailto:sales@overhoff.com)  
WEB [www.OVERHOFF.com](http://www.OVERHOFF.com)