

NEUTRON REM AREA MONITORING SYSTEM

Model ~ FM-7 REM

FEATURES:

- ON-LINE REAL-TIME NEUTRON MONITORING
- ALL PLUG-IN MODULAR
- RACK MOUNTING OR CASE
- SINGLE OR MULTI-CHANNEL
- LOCAL OR REMOTE MONITORING
- HIGH LEVEL ALARM, SOLID STATE, NON-CONTACTING
- RS-232 OUTPUT FOR PRINTER, PC, AND REMOTE DISPLAY
- ON BOARD COMPUTER OF DATA MEASUREMENT & DISPLAY



APPLICATION:

Neutron Area Monitoring in and around nuclear reactors, accelerators, neutron sources and generators, etc.

DESCRIPTION:

The FM-7-REM provides dependable, accurate digital Electronics and Readout, Power supply, Alarm Module.

The energy compensated BF₃ Probe offers Neutron sensitivity from thermal to >100 MeV, and close following of true REM response from thermal to >7 MeV along with high Gamma rejection.

The plug-in modular construction, allows for additional channels to be added.

The built-in anti-saturation circuit prevents the system readings from falling off scale during an over-range condition.

High level alarm can be set at any point on the scale. Activation produces flashing red light on front panel and piercing intermittent 2000 Hz tone. Relay. It can also closed (or opened) for activation of remote alarms.



TECHNICAL ASSOCIATES
OVERHOFF TECHNOLOGY

7051 Eton Ave., Canoga Park, CA 91303
818-883-7043 (Phone) 818-883-6103 (Fax)

tagold@nwc.net

WWW.TECH-ASSOCIATES.COM

Divisions of



US NUCLEAR CORP

NEUTRON REM AREA MONITORING SYSTEM

Model ~ FM-7 REM

SPECIFICATIONS

Range:	5 decades 0.1 mRem to 10 Rem/hr.
Readout:	6 digit high visibility LEDS.
Accuracy:	±10% of decade. ± 1 count.
Front Panel Controls:	High Level Alarm Set High Voltage Adjust (internal) Intermediate Level Alarm Set Power On-Off Switch Alarm Reset Pushbutton
Time Constant:	Varies inversely with count rate.
Output:	RS-232 output to Printer, computer, etc. User Settable.
Detector:	Moderated proportional BF ₃ neutron tube. Supplied with 8 ft. cable.
Detector Response:	Neutrons from thermal to > 100 Mev. Energy matched by LASL designed moderating sphere to ICRP tissue response curve from thermal to above 7 MeV.
Energy Dependence:	Closely follows true REM curve from thermal to above 7 Mev. Sensitive to >100 Mev.
Environmental Temperature:	Operating range between -30°C and 65°C; 0-95% humidity non-condensing.
Data Processing:	Counts energy compensated pulses to give direct mRem/hr (or other presettable unit e.g. μ Sv/h.) RS-232 output.
High Level Alarm:	Activated when count rate exceeds set point. High-level red light on front panel goes on in addition to Beeper and Flasher. (Latching or Unlatching)
Intermediate Level Alarm:	Level settable below High Level Alarm to warn of unusual rad level before alarm level is reached. Amber light on front panel goes on in addition to sonalert. (Not latching)
Anti-Saturation:	Circuitry prevents readings from falling below full scale in over-range conditions.
Line Operation:	105-125V (or 200-240 V), 50-60 Hz.

WEIGHT & DIMENSIONS:

Dimensions:	Console: 10-1/4" W x 8-3/4" H x 12-1/2" D single channel - (wider if more than one channel) or rack mount. Probe: 10" round by 16" H.
Weight:	Console: 20 lbs. Probe: 20 lbs.
Mounting:	Electronics are normally furnished in FM-7 case but can be furnished uncased with mounting bars for rack or Nema 4 (hostile environment) cabinet.

OPTIONS:

Emergency Power: Stand-by batteries automatically take over providing approximately eight hours operation in the event of AC power failure. Battery life will be shortened in alarm conditions.

Multiple channel systems.	Standby batteries.
Solenoid activated check source for system calibration.	Cable to 500 feet.
Remote alarm-flasher-howler	Power Input 12V DC or 200-240V 50-60 Hz.
Remote readout with alarm.	



TECHNICAL ASSOCIATES
OVERHOFF TECHNOLOGY

Divisions of



US NUCLEAR CORP

7051 Eton Ave., Canoga Park, CA 91303
818-883-7043 (Phone) 818-883-6103 (Fax)

tagold@nwc.net

WWW.TECH-ASSOCIATES.COM